SOLENOID VALVES | Special Purpose

Isolated


GEM-C | Chem-Sol 1/2" 2 Way NC






1/2" | Vacuum

with Manual Override





Technical Data

| Function | 2 Way NC | | | | | | | |
|------------------------------------|--|--|--|--|--|--|--|--|
| Ports size | 1/2" BSP & NPT | | | | | | | |
| Orifice size | 8mm | | | | | | | |
| Pressure range | See table | | | | | | | |
| Kv (l/min) | 18 l/min | | | | | | | |
| Temperature range | Fluid : 5°C to 50°C (no freezing) Ambient : -10°C to 50°C | | | | | | | |
| Materials in contact with media | Manual override: Plastic * Available for vacuum application only Main Valve: PVC Seals: FPM (Viton®), EPDM | | | | | | | |
| Applications | Chemical process Water treatment Analysis device etc | | | | | | | |
| Coil voltage | Voltage and power consumption - see table All Baccara coil voltages are from -5% to ±10% of nominal | | | | | | | |
| Standard protection class | IP65 with connector * Option : IP68 (please refer to GEM-BP Coil) | | | | | | | |

• Supplied with mounting threads on request, please specify.

Pressure (bar) table NC

| Coil | | Flow direction not restricted | Flow direction restricted |
|------|--------------|----------------------------------|------------------------------|
| | AC 8W, DC10W | 0 to 0.7 bar | Min dp 0.3 bar |

Vacuum (bar) table NC

| Coil | Flow direction not restricted | Flow direction restricted | | | | | |
|---------|----------------------------------|------------------------------|--|--|--|--|--|
| AC 8W | -1 to 0.5 bar | -1 to 0.5 bar | | | | | |
| AC 5.5W | -0.5 to 0.5 bar | -0.8 to 0.5 bar | | | | | |
| DC 10W | -0.4 to 0.5 bar | -0.6 to 0.5 bar | | | | | |

Voltage & Power Consumption

| | | 50 Hz | | | 60 Hz | | DC (W) | | | | | | |
|-----|-----|-------|-----|-----|-------|-----|--------|-----|-----|--|--|--|--|
| V | 8 | 5.5 | 2.5 | 8 | 5.5 | 2.5 | 10 | 5.5 | 3.5 | | | | |
| 6 | | | | | | | • • | | | | | | |
| 12 | • • | | | • • | | | • • | | | | | | |
| 24 | • • | • | | • • | • | | • • | | | | | | |
| 48 | • • | | | • • | | | • • | | | | | | |
| 110 | • • | | | • • | • | | • • | | | | | | |
| 120 | • • | | | • • | | | | | | | | | |
| 220 | • • | • | | • • | • | | • • | | | | | | |
| 230 | • • | • | | | | | | | | | | | |
| 240 | • • | | | • • | | | • • | | | | | | |

Available options:

Vacuum

Pressure

How to Order

| HOW to | U | raer | | | | | | | | | | | current an | id pr | ressure rati | ng i | is needed (DC, | AC) | | |
|----------|-----------|----------|----|-------|---|----------|-------------|-----------------|--------------------------------|-------------|------|------------|---------------|-------|----------------|------|------------------------------------|-----|-----------|--|
| GEM-C | - PORT | | - | PORT | | FUNCTIO | DN | PRESSUR | E | SEALS | | MANUAL OVE | RRIDE | - | VOLTAGI | E | POWER | | CONNECTOR | |
| | | 1/2" BSP | 40 | 2W NC | 1 | Vacuum | 1 | FPM (Viton®) | v | None | Null | | W/out coil | 0 | No coil | 0 | without | 0 | | |
| | | 1/2" NPT | 41 | | | Pressure | 2 | EPDM | E | Plastic (1) | 1 | | 6 | 1 | AC8W 50Hz | 1 | with | 1 | | |
| | | | | | | | | | | | | | 12 | 2 | AC8W 60Hz | 2 | with LED | 2 | | |
| | | | | | | | | | | | | | 24 | 3 | DC10W | 3 | with bi- color LED | 3 | | |
| | | | | | | | | | | | | | 48 | 4 | AC5.5W 50Hz | 4 | flying leads coil | 4 | | |
| | | | | | | | | | | | | | 110 | 5 | AC5.5W 60Hz | 5 | with 1/2" Hub | 5 | | |
| | | | | | | | | | | | | | 120 | 6 | | | surge protec- tion with LED | 6 | | |
| | | | | | | | | | | | | | 220 | 7A | | | connector with moulded cable | 7 | | |
| | | | | | | | | | | | | | 230 | 7 | | | other | 9 | | |
| | | | | | | | | | | | | | 240 | 8 | | | | | | |
| | | | | | | | | | Latch/ other ⁽²⁾ | 9 | | | | | | | | | | |
| GE 00E 0 | · · · · · | | | | | | • · · · · · | | | | | | | | | | | | | |

GEM-SOL Chem-Sol, 1/2"BSP, 2W NC for vacuum, FPM (Viton®), plastic manual override, 24V AC 8W 60Hz with connector.




(1) Available for Vacuum application only

(2) For specifying Latch type coil, please refer to GEM-A3P valve - How to Order table



Isolated | GEM-SOL | Chem-Sol 1/2" 2 Way NC



With Manual Override

* When ordering without coil, please define what